



IR157N

ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

Patient Station(s) shall be Alpha Communications®/Tektone model IR157N, or approved equal. Model IR157N shall include solid-state call-placed and intercom in-use LED indicators, call cord or pillow speaker jack, cancel button, and a 3.50" speaker/microphone with voice response. It is mounted on a rugged extruded aluminum faceplate. Positive crew terminals shall be used for electrical connections. IR157N shall be flush mounted to the model IH106N flush back box/housing.

Contractor shall observe all local and national electrical and building codes.

IR157N Single Patient Station

The Alpha Communications® IR157N Patient Station provides for efficient use of the nursing staff by permitting fast and reliable communication between nurse and patient. Calling the nurse is accomplished by pressing the area of the pillow speaker designated by the "☎" symbol or by pressing the call button on the end of the (optional) SF311 or SF312 call cord. Call-placed assurance and intercom operation is indicated by reliable solid-state L.E.D. indicators. A non-cancelable call is registered if the call cord is removed from the jack. A reset button is provided on the patient station.

When used with the SF301P pillow speaker, the IR157N also provides for television control directly from the station. To operate, push the area of the pillow speaker designated "TV". If television is off, it will come on. Each additional push will change the channel until the TV is turned off when the cycle is completed.

FEATURES

- Push button calling
- TV control from pillow speaker
- Call reset push button
- Call-placed indicator
- Sensitive speaker/microphone
- Intercom indicator lights when room is monitored
- Attractive brushed-aluminum faceplate

SPECIFICATIONS

| | |
|----------------------|---|
| Dimensions: | Height: 5.00" (127mm) |
| | Width: 6.87" (157mm) |
| | Depth: 2.00" (50mm) |
| | Projects: 0.50" (13mm) |
| | above mounting surface |
| Construction: | Rugged extruded aluminum faceplate with Black ABS plastic speaker grill |
| Finish: | Brushed aluminum (anodized) |
| Speaker/Mic: | 3.50" (90mm) with voice response |
| Connections: | Positive Screw terminals |
| Housings: | Flush mounting box (IH106N) horizontal mount |

SF301P Pillow Speaker/Features

| | |
|---------------|--|
| Application: | Use with station IR157N |
| Cord: | One-piece molded 6' long. |
| Push Buttons: | Momentary contact for nurse-call and T.V. controls |

- S.P.S.T. Switch
- Dirt and dust protection
- Switch soldered into printed circuit board
- Lightweight-fits comfortably in hand

Due to continuous product improvement, all colors, sizes, materials, finishes and specifications are subject to change without notice.