




SF301PIR2L (shown)

ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

Pillow Speaker(s) shall be Alpha Communications®/Tek-tone model SF301P series (*specify model here*) or approved equal. It shall have a 2.75" Mylar cone speaker. The pillow speaker case shall be constructed of ABS Flame retardant plastic. All momentary contact SPST 10 AMP switches shall be rated for over 1,000,000 operations. The pillow speaker cord shall be standard telephone type 8 conductor cable and shall have a modular plug. The cord shall also be provided with stain relief. Each pillow speaker shall be provided with a wall hanger, a security/bed clip and its own individual plastic bag.


Controls shall be provided (as required) for entertainment, audio, intercom, nurse calling and channel selection of television, and shall be marked , TV, RADIO, respectively.

The pillow speaker shall be Electro-Static-Discharge protected to over 20,000 volts. The pillow speaker(s) shall be UL 1069 listed to the latest 4th Edition standards.

SF301P Series Pillow Speakers with optional features

The Alpha Communications® SF301P series pillow speaker are used primarily with the IR311/IR312 room stations for the NC300 and/or NC300II series microprocessor nurse-call system.

Various models provide for call placement to the system station master(s), for TV controls, radio controls, and single or dual lamp controls. Simple operation is provided by momentary switches.

To call a nurse or select television or radio channels simply press the pushbutton indicated "". Separate pushbuttons are provided for TV and radio on/off, and channel selection. TV and radio sound is automatically silenced while the intercom is in use.

FEATURES

- UL 1069 Listed - 4th Edition standards
- Mylar cone speaker
- ABS flame-retardant plastic
- SPST 10 AMP switches - rated for over 1 million operations
- ESD protected over 20,000 volts
- Hanger and security/bed clip provided
- Standard telephone type 8 conductor cord with modular plug

MODELS AVAILABLE

<u>SF301P</u>	Call, TV volume, TV select
<u>SF301PI</u>	Call, TV volume, TV select, Intercom
<u>SF301PL</u>	Call, TV volume, TV select, 1 Light Control
<u>SF301PR</u>	Call, TV volume, TV select, Radio select
<u>SF301PIL</u>	Call, TV volume, TV select, Intercom, 1 Light Control
<u>SF301PRL</u>	Call, TV volume, TV select, Radio select, 1 Light Control
<u>SF301PR2L</u>	Call, TV volume, TV select, Radio select, 2 Light Controls
<u>SF301PIR</u>	Call, TV volume, TV select, Intercom, Radio select
<u>SF301PIRL</u>	Call, TV volume, TV select, Intercom, Radio select, 1 Light Control
<u>SF301PIR2L</u>	Call, TV volume, TV select, Intercom, Radio select, 2 Light Controls
<u>SF301PI2L</u>	Call, TV volume, TV select, Intercom, 2 Light Controls

Due to continuous product improvement, all colors, sizes, materials, finishes and specifications are subject to change without notice.