



Product Specification Sheet



APS439

Rev. 2 - 08/2003



IR151B



IR152B

ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

Patient Station(s) shall be Alpha Communications®/Tek-tone IR151B and/or IR152B, or approved equal. Model IR151B shall contain call-placed and intercom in-use indicators, cancel button, call cord jack and a 2.50" speaker/microphone with voice response. Model IR152B shall include all of above with an additional call cord jack and call-placed indicator.

Removal of a cord, either accidentally or intentionally, will place a call, which can be canceled only by replacing the cord or its equivalent into the call jack. All station components shall be mounted on an attractive flame retardant ABS plastic faceplate, in fog white color. Connections shall be plug-in type. The station(s) shall be use a 2.50" x 2.50" speaker/microphone for accurate voice reproduction.

Contractor shall observe all local and national electrical and building codes.

The IR151B and IR152B station(s) shall be UL 1069 listed to the latest 4th Edition Standards

Copyright© 2000-2003, Alpha Communications®, All Rights Reserved

IR151B Single Bed Patient Station

The Alpha Communications® IR151B Patient Station provides for efficient use of the nursing staff by permitting fast and reliable audio communication between nurse and patient.

Calling the nurse is accomplished by pressing the call button on the end of the 8 to 10 foot long call cord. A non-resettable call is registered if the call cord is accidentally removed from its jack. Call-placed assurance and intercom operation is indicated by reliable solid state LED indicator lamps.

The speaker/microphone is sensitive enough to assure clear conversations even with weak patients. A call reset button is also provided on the rugged ABS plastic faceplate.

IR152B Dual Bed Patient Station

Same specifications and features as the IR151B except that it includes two call cord jacks and two call-placed indicators for use with two patient beds (in close proximity to each other).

FEATURES

- Call reset push button
- Intercom indicator lights when room is monitored
- Push button calling from call cord(s)
- Call-placed LED indicator(s)
- Sensitive speaker/microphone

SPECIFICATIONS

Dimensions: Height: 4.50" (119 mm)
 Width: 6.38" (162 mm)
 Depth: 2.75" (70 mm)
 Projects: 0.50" (12.7mm) above mounting surface

Construction: Attractive, flame retardant ABS plastic

Finish: Light texture, fog white color.

Speaker: 2.50" x 2.50" with voice response

Connections: Plug-in type

Housing: Steel City #H3BD with Steel City #3GC plaster ring, or Alpha Communications® part #IH353 box with IH352 ring, or EXACT EQUAL. Horizontal mount.

SF301/8 or SF301/10 Call Cord Switch

Use SF301/8 (8 foot) or SF301/10 (10 foot) call cord, or other specialty type (i.e. Geriatric type). Includes HW155 pillow/bedsheet clip.

Cord Construction: One piece molded, 8' or 10' long

Push Button: Momentary contact

Due to continuous product improvement, all colors, sizes, materials, finishes and specifications are subject to change without notice.