



IR216

ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

Psychiatric station(s) shall be Alpha Communications®/Tektone Model IR216 or approved equal and shall be supervised from the central equipment. Model IR216 shall include solid state LSI/microprocessor technology, yellow call-placed indicator, key switch, and combination red in-use indicator and reset button.

Activation of the key switch shall place a non-resettable call at the nurse master station and shall power enable the staff emergency button on the associated staff emergency station. The key switch shall not deactivate the speaker/microphone station.

All station components shall be mounted on a rugged extruded aluminum panel. Connections shall be plug-in type.

Contractor shall observe all local and national electrical and building codes.

Copyright© 1999-2007, Alpha Communications®, All Rights Reserved

IR216 Enhanced Psychiatric Station

The IR216 Enhanced Psychiatric Station provides for audible, visual and digital communication to and from the Central Equipment, including the nurse's master station(s). The station is intended for use in psychiatric wards or other high security hospital areas and is normally flush mounted at the entrance to these areas.

Activation of the station key switch places a non-resettable call to the nurse master station(s) and power enables the associated staff emergency station (model SF336 or SF338) located in the ward. Call placement is indicated by the call-placed light on the station panel and at the associated dome lamp. The in-use light on the panel indicates that the ward is being monitored at the nurse master station via the speaker/microphone located in the ward. If a staff member should require emergency assistance, the staff emergency station (model SF336 or SF338) can be used to place an emergency call to the master.

When exiting the ward, the staff member will turn the key switch to the "OFF" position and push the reset button to deactivate the emergency button and cancel the call at the master station. The speaker/microphone will remain active should a staff member wish to monitor that particular area.

FEATURES

- Places non-resettable call to master station(s)
- Programmable call priority
- Monitor capability
- Solid-state circuitry
- Supervised
- 4 Bulb Dome Light outputs
- Simplified wiring using plug-in type connectors
- Presence Station input
- Attractive brushed anodized aluminum extruded faceplate

SPECIFICATIONS

Dimensions:	Height: 5.00" (127mm) Width: 6.88" (175mm) Depth: 2.75" (70mm) Projects: 0.25" (6.5mm) above mounting surface
Construction:	Rugged, extruded anodized aluminum faceplate
Finish:	Brushed aluminum (clear anodized)
Connections:	Plug-in type
Housing:	Alpha Communications® model IH353 box with IH352 ring (or Steel City #H3BD with Steel City #3GC plaster ring), or EXACT EQUAL. Horizontal mount.
Wiring:	1 twisted shielded pair #18AWG common, plus 4 conductor #18AWG common, plus 1 conductor #22AWG selective.

Due to continuous product improvement, all colors, sizes, materials, finishes and specifications are subject to change without notice.